

Cerniera a 2 ali per aperture interne


2 wing hinge for internal openings

Paumelle à 2 lames pour ouvertures intérieures

Bisagra de 2 alas para aberturas internas

2 Flügeliges Band (Innen öffnend)

Двухсекционная петля для внутреннего открывания



Asportare la guarnizione



Remove the gasket

Enlever le joint

Sacar la junta

Dichtung entfernen

Удалить уплотнитель



Sequenza di montaggio

Sequence assembly

Séquence de montage

Secuencia de montaje

Montage Reihenfolge

Последовательность монтажа




Tabella di adattabilità per profili italiani

Suitability table for italian profile

Estrusore	Profilo
SAPA	R40/50 TT barra cont./60 TT/62 TT/72 TT
PONZIO SUD	NEW TEC 50/52/60F/60 TT/68 TT
CLL	TECNO 50/50 TT/60 TT/68 TT
ETNALL	40500/TT50
ALLU SISTEMI	RX600/RX700
PRESAL EXTRUSION	PR66TT/PR75TT